



List of standard and options

| | | NTS10 | NTS20 | TTS10 | TTS20 | |
|------------|---|--------------|-------|-------|-------|---|
| Robot arm | Robot: single arm | ●*2 | - | ●*2 | - | |
| | Robot: double arm | - | ●*2 | - | ●*2 | |
| | Z-stroke (470mm) | ● | ● | - | - | |
| | Z-stroke (740mm) | - | - | ● | ● | |
| | Hand specification*1 | Edge gripper | ○ | ○ | ○ | ○ |
| | | Vacuum | ○ | ○ | ○ | ○ |
| | Mapping sensor | ○ | ○ | ○ | ○ | |
| Aligner | Aligner | ○ | ○ | ○ | ○ | |
| Controller | D60 controller | ● | ● | ● | ● | |
| | Jig for programming | ○*3 | ○*3 | ○*3 | ○*3 | |
| | Teach pendant | ○*3 | ○*3 | ○*3 | ○*3 | |
| | Robot harness (1, 2, 2.5, 3, 3.5, 4, 4.5, 5 meters) | ●*4 | ●*4 | ●*4 | ●*4 | |
| Software | Standard software for operation | ● | ● | ● | ● | |
| | KMTerm | ● | ● | ● | ● | |
| | KSUtility Lite | ● | ● | ● | ● | |
| | KRET | ○ | ○ | ○ | ○ | |
| | KR3D | ○ | ○ | ○ | ○ | |
| | KSUtility | ○ | ○ | ○ | ○ | |
| Manual | Operation manual | ● | ● | ● | ● | |
| | Communication command manual | ● | ● | ● | ● | |
| | Introduction procedure for Integrated package software (K-Fast) | ● | ● | ● | ● | |
| Training | Programing, maintenance, troubleshooting | ○ | ○ | ○ | ○ | |

●:Standard ○:Option -/:Not Selectable
 *1: The standard robot arm does not include a hand.
 *2: Either the edge grip or vacuum hand can be used.
 *3: When selecting a teach pendant, an operation box is also needed.
 *4: Select a robot harness with the length between 1 and 5 meters.
 Contact Kawasaki representatives in your region.

Kawasaki Robot Clean Robot NTS, TTS series



Kawasaki Heavy Industries, Ltd.

Robot Business Division

Tokyo Head Office/Robot Division
 1-14-5, Kaigan, Minato-ku, Tokyo 105-8315, Japan
 Phone: +81-3-3435-2501 Fax: +81-3-3437-9880

Akashi Works/Robot Division
 1-1, Kawasaki-cho, Akashi, Hyogo 673-8666, Japan
 Phone: +81-78-921-2946 Fax: +81-78-923-6548

Global Network

Kawasaki Robotics (USA), Inc.
 28140 Lakeview Drive, Wixom, MI 48393, U.S.A.
 Phone: +1-248-446-4100 Fax: +1-248-446-4200

Kawasaki Robotics (UK) Ltd.
 Unit 4 Easter Court, Europa Boulevard, Westbrook Warrington
 Cheshire, WA5 7ZB, United Kingdom
 Phone: +44-1925-71-3000 Fax: +44-1925-71-3001

Kawasaki Robotics GmbH
 Im Taubental 32, 41468 Neuss, Germany
 Phone: +49-2131-34260 Fax: +49-2131-3426-22

Kawasaki Robotics Korea, Ltd.
 43, Namdong-daero 215beon-gil, Namdong-gu, Incheon, 21633,
 Korea
 Phone: +82-32-821-6941 Fax: +82-32-821-6947

Kawasaki Robotics (Tianjin) Co., Ltd.
 1-2/F, Building 6, No.19 Xinhuan Road, TEDA, China
 Phone: +86-22-5983-1888 Fax: +86-22-5983-1889

Kawasaki Motors Enterprise (Thailand) Co., Ltd.
 (Rayong Robot Center)
 119/10 Moo 4 T.Pluak Daeng, A.Pluak Daeng, Rayong 21140
 Thailand
 Phone: +66-38-955-040-58 Fax: +66-38-955-145

<https://robotics.kawasaki.com/>

* Materials and specifications are subject to change without notice.

Kawasaki Robot

CAUTIONS TO BE TAKEN TO ENSURE SAFETY

- For those persons involved with the operation / service of your system, including Kawasaki Robot, they must strictly observe all safety regulations at all times. They should carefully read the Manuals and other related safety documents.
- Products described in this catalogue are general industrial robots. Therefore, if a customer wishes to use the Robot for special purposes, which might endanger operators or if the Robot has any problems, please contact us. We will be pleased to help you.
- Be careful as Photographs illustrated in this catalogue are frequently taken after removing safety fences and other safety devices stipulated in the safety regulations from the Robot operation system.



ISO certified in Akashi Works.

Horizontal Articulated Arm NTS series



Features:

- A single robot can access 2 and 3 FOUPs of EFEM without a track.
- Smooth operation. The specially designed drive system enables the robot to move incredibly smoothly and deliver high precision.
- Compliant with SEMI-F47 standard.
- Compliant with SEMI-S2 standard. Sufficient considerations given to the environment and personal safety.


Specifications

| Model | NTS10 | NTS20 |
|--------------------------|------------------------------------|-------|
| Structure | Horizontal articulated type | |
| Degree of freedom (axes) | 4 | 5 |
| Motion range | $\theta 1$ axis (rotation JT2) (°) | 340 |
| | Z axis (up-down JT3) (mm) | 470 |
| | $\theta 2$ axis (rotation JT4) (°) | 340 |
| | H1 axis (rotation JT6) (°) | 340 |
| | H2 axis (rotation JT7) (°) | — |
| Maximum reach (mm) | 1,066 | |
| Repeatability (mm) | ±0.1 (Wafer Center) | |
| Cleanliness*1 | ISO Class 1 | |

*1: Measured in our clean booth

Layout Example

The NTS and TTS series can be used for 2 to 3 FOUPs of EFEM without a track. (The same arm can be used for 2 FOUPs and 3 FOUPs).



Horizontal Articulated Arm TTS series



Features:

- All the features of the NTS series have been carried over to the TTS series, including the ability to access up to 3 FOUPs.
- Kawasaki's unique and highly rigid telescopic mechanism delivers high-speed handling in high and low positions.
- Compliant with SEMI-F47 standard.
- Compliant with SEMI-S2 standard. Sufficient consideration given to the environment and personal safety.

Specifications

| Model | TTS10 | TTS20 |
|--------------------------|--|-------|
| Structure | Telescopic horizontal articulated type | |
| Degree of freedom (axes) | 4 | 5 |
| Motion range | $\theta 1$ axis (rotation JT2) (°) | 340 |
| | Z axis (up-down JT3) (mm) | 740 |
| | $\theta 2$ axis (rotation JT4) (°) | 340 |
| | H1 axis (rotation JT6) (°) | 340 |
| | H2 axis (rotation JT7) (°) | — |
| Maximum reach (mm) | 1,066 | |
| Repeatability (mm) | ±0.1 (Wafer Center) | |
| Cleanliness*1 | ISO Class 1 | |

*1: Measured in our clean booth

Software

Standard software

The standard software best suits robot operations for wafer handling and allows monitoring of operating conditions.

KMTerm

By connecting with the robot controller, the KMTerm allows parameter setting, information display and data backup.

KSUtility Lite

The KSUtility Lite enables the robot to be operated from the host PC.

Optional Software

Optional software allows the user to perform layout studies and simulation for tact time on their own PC.

KRET

Designing of layout inside the equipment and operational paths can be done with ease.


KSUtility

Enables the robot to be operated from the host PC.

KR3D

Robot operations can be performed off-line with ease.

*For details of the software, see relevant manuals.



Hand (Option)



Edge gripper hand




Vacuum hand

*For details of the software, see relevant manuals.

Aligner (Option)

Features:

- High-speed alignment (time for alignment per se is 2.5 seconds only).



*For details of the software, see relevant manuals.

Controller

Features:

- Compact package. Compliant with SEMI-F47 standard.
- Ethernet communication port installed as standard enables high-speed communications.
- Allows flexible processing of various kinds of software.



D60 Controller

*For detail specifications, contact Kawasaki representatives in your region.



SERVICIO TÉCNICO, CONSULTORÍA, TRAINING Y CANAL DE VENTA OFICIAL

Instalaciones centrales

Francisco Aristeguieta Centro Tecnológico (F.A.C.T.)
GI-3162 (Zarautz – Urdaneta) km 2,2
E-20809 AIA (Gipuzkoa), Spain

www.larraioz.com

Tel. (+34) 943 140 139
Fax. (+34) 943 140 327
E-mail. info@larraioz.com



Instalaciones en Getaria

Larraioz Etxea, Eizaga Auzoa,
Garate Mendi E-20808
GETARIA (Gipuzkoa), Spain

Instalaciones América Latina

Carlos Calvo 2480, B8000XAV
Buenos Aires (Buenos Aires),
Argentina

Dirección postal

Larraioz Electrónica Industrial,
S.L. Apartado de Correos
193 E-20800 ZARAUTZ
(Gipuzkoa), Spain



Mechatronics & Robotics



Industrial Automation



Industry 4.0



Vision